

# Specialty Materials™



THE BEST GARMENT DECORATION PRODUCTS

# LOVE what you PRESS!



## TRANSFER TAPES

Name	Tackiness	Opacity	Liner	Compatible with:	Size Available
Transfer & Seal Tape Paper Based with Rubber Adhesive	Medium	Opaque	No Liner	ColorPrints, ColorPrint Solvents	Width: 12", 16", 24" Length: 60'
TM-850 PET w/Acrylic Adhesive	Strong	Transparent	Has Liner	Ultimate Print Nylon	Width: 20", 30", 60" Length: 30' and 90'
TM-853 PET w/Acrylic Adhesive	Light Medium	Transparent	Has Liner	ColorPrints, ColorPrint Solvents	Width: 20" and 30" Length: 30'
TM-854 PET w/Acrylic Adhesive	Medium	Transparent	Has Liner	ColorPrints, ColorPrintSolvents, Solvent Flock	Width: 20" and 30" Length: 30'
DTM-855 PET w/Acrylic Adhesive	Very Light	Transparent	No Liner	ColorPrint Solvents	Width: 12", 16", 25", and 50" Length: 60'
KTM-500/1000 PET w/Acrylic Adhesive	Strong	Transparent	Has Liner	Ultimate Print Matte and Gloss, Rhinestones, Subblocker Printable, Reflective Printables RP-MSSIL and RP-MSWH, Printable Blockout	Width: 19.5" Length: 30', 75', and 162' 1000: 39" x 162'
HFIX-SIL PET w/Silicone Adhesive	Very Strong	Transparent	Has Liner	Large rhinestones or rhinestuds	Width: 38" Length: 30', 75', and 162'
HFIX-LOW PET w/Acrylic Adhesive	Light	Transparent	Has Liner	Ultimate Print Nylon	Width: 38" Length: 30', 75', and 162'
HFIX-FLCK PET w/Acrylic Adhesive	Very Strong	Transparent	Has Liner	EcoPrint, GlitterFlex Printable, Twill, Glitter Twill	Width: 38" Length: 30', 75', and 162'

\*PET resists high temperatures. PET masks are not recommended for use with the sublimation process, because PET sublimates.

\*Printable materials that do not require a transfer mask: Aquaprint Clear & Opaque, Clear Matte and Clear Gloss, Color Jet III Light & Dark, CL Light, CL Trim Free, and CL Dark Premium

### Thickness

DTM-855, TM-850, TM-854, TM-853: 4 mils/100 microns

## THERMO TAPE

Sizing Available: .35" x 215'

A silicone based tape used to position multi-piece designs, such as names, numbers and more, before heat pressing. After pressing, the tape is removed without leaving any sticky residue.



**Technical Support: Toll Free: 877-437-8556 | SpecialtyMaterials.com**

All technical information and recommendations are based on tests we believe to be reliable. However, we cannot guarantee performance for conditions not under manufacturer's control. Before using, please determine the suitability of product for its intended use. The user assumes all risk and liability whatsoever in connection with the use of this product. Seller's and manufacturer's only obligation shall be to replace such quantity of the product proved to be defective by manufacturer.

Copyright © 2020, Specialty Materials & Digital Decoration, LLC. All rights reserved. Tulsa, OK 74107